

Skærepakke

Panels may need to be cut to precise heights and widths in some environments. The X-Guard cutting pack can be used to help you cut panels and is available in both vertical and horizontal versions.




The vertical comes in four heights; 750, 1300, 1900 and 2200 mm. The horizontal only comes in 1500 mm but is compatible with all widths and is available with or without attachments to allow unrestricted positioning. The standard cutting pack colour is black (RAL 9011) but customised colours are available upon request.

A rubber strip can be fitted to provide a soft and neat edge where mesh panels have been cut.

Modeller

Lodret 8 artikler


| ARTIKLER / BESKRIVELSE | MAKS. BREDE (MM) | HØJDE (MM) | FARVE |
|---|------------------|------------|---------------------------|
|  KVL-3-130 Vertical, X-Guard Lite | | 1300 | Graphite Black (RAL 9011) |
|  KVC-3-075 Vertical, X-Guard Classic | | 750 | Graphite Black (RAL 9011) |

| | | | |
|---|---|------|---------------------------|
|  | KVC-3-130 Vertical, X-Guard Classic | 1300 | Graphite Black (RAL 9011) |
|  | KVL-3-190 Vertical, X-Guard Lite | 1900 | Graphite Black (RAL 9011) |
|  | KVC-3-190 Vertical, X-Guard Classic | 1900 | Graphite Black (RAL 9011) |
|  | KVL-3-220 Vertical, X-Guard Lite | 2200 | Graphite Black (RAL 9011) |
|  | KVC-3-220 Vertical, X-Guard Classic | 2200 | Graphite Black (RAL 9011) |
|  | KVC-3-240 Vertical, X-Guard Classic | 2400 | Graphite Black (RAL 9011) |

Vandret 3 artikler

| ARTIKLER / BESKRIVELSE | MAKS. BREDE (MM) | HØJDE (MM) | FARVE |
|---|------------------|------------|---------------------------|
|  KH-3-150 Horizontal, incl. fittings K1-01 | 1500 | | Graphite Black (RAL 9011) |
|  KH-3-150B Horizontal, excl. fittings K1-01 | 1500 | | Graphite Black (RAL 9011) |
|  KHE-3-150 Skæringspakke 19x19 vandret | 1500 | | Graphite Black (RAL 9011) |

Relaterede produkter



Kantstrimmel

X-Guard edge strip is available in two versions. 1) The rubber edge strip gives a soft and neat edge in places where the mesh panel has been cut out. 2) With the wider rubber strip, T01-21, intende...

2 artikler